



WILCO without cuff (PPE - category II)

FIELD OF APPLICATION

The WILCO glove provides protection against stabbing when:

- working in slaughter houses, in meat, fish or shellfish industries
- working in catering establishments
- doing manual boning operations for processing meat, game and poultry
- working in plastics, leather, textile and paper industries
- laying floor coverings and similar works




MATERIAL : food contact stainless steel wire and food contact stainless steel patented spring.

FEATURES

Chainmail :

- wire diameter : 0,5 mm
- ring internal diameter : 3 mm
- ring external diameter : 4 mm

Wrist fastening with stainless steel spring protected by mesh
Reversible left-handed glove (GA) or reversible right-handed glove (DR)
Size of the glove identified by a colour tag



NORMS & REGULATIONS

This glove complies with the regulation (UE) PPE 2016/425.

NF EN 1082-1 & ISO 13999-1: Protective clothing. Gloves and armguards protecting against cuts and stabs from hand knives

NF EN 14328: Protective clothing. Gloves and armguards protecting against cuts from powered knives. Requirements and test methods

Stainless steel in accordance with **NF A 36-711** regulation: « Steel other than for packaging - Stainless steel intended to come into contact with foodstuffs, products and drinks for humans or animals » and with **NF EN 1811 + A1** regulation «Reference test method for release of nickel from products intended to come into direct and prolonged contact with the skin»

Glove in accordance with **article 33 of REACH** regulation (Registration, Evaluation, Authorisation and Restriction of Chemicals) **N°1907/2006** - 18 december 2006 and its amendments.

Notified body : N° 0556 : DGV test Prüf und Zertifizierungsstelle Nahrungsmittel und Verpackung
Fachbereich Nahrungsmittel - Lortzingstasse 2 - D - 55127 Mainz



CLEANING

Cleaning: PPE cleaning is performed using an appropriate cleaning gun, by vigorous brushing or in a washing machine. In any case, the water temperature should be between 50 and 55°C max. Only use products authorised for food contact by health services. High chlorine dose is not recommended.

Strictly follow the cleaning instructions noted in the product's instructions for use.

Rinsing: with water. **Storage:** in a dry and ventilated place.

SIZE AND REFERENCES

	BLACK / 00 / XXXS / 4 - 4^{1/2} OGWO.131.000.000.GA OGWO.131.000.000.DR		BROWN / 0 / XXS / 5 - 5^{1/2} OGWO.131.00.000.GA OGWO.131.00.000.DR		GREEN / 1 / XS / 6 - 6^{1/2} OGWO.131.10.000.GA OGWO.131.10.000.DR		WHITE / 2 / S / 7 - 7^{1/2} OGWO.131.20.000.GA OGWO.131.20.000.DR
	RED / 3 / M / 8 - 8^{1/2} OGWO.131.30.000.GA OGWO.131.30.000.DR		BLUE / 4 / L / 9 - 9^{1/2} OGWO.131.40.000.GA OGWO.131.40.000.DR		YELLOW / 5 / XL / 10 OGWO.131.50.000.GA OGWO.131.50.000.DR		PURPLE / 6 / XXL / 11 OGWO.131.60.000.GA OGWO.131.60.000.DR

N° intrastat : 73239300

Bien plus que la sécurité
More than just safety



Postal adress: CS 40055 - 49170 - SAINT-GEORGES-SUR-LOIRE - France - E-mail: manulutex@manulutex.fr - Internet: www.manulutex.fr
Factory of Champocé-sur-Loire: Zone Artisanale du Mille - 49123 CHAMPTOCÉ-SUR-LOIRE - France - Tel: +33 (0)2 41 39 90 30 - Fax: +33 (0)2 41 39 99 11

Version n°1 - 02/04/2020 - Document and pictures are not contractuals